

Eaton RD63-3-508

Catalog Number: RD63-3-508

Eaton Bussmann series RD non-fused rotary disconnect switch, Front/side handle operation, 600V, 63A, Non-fused disconnect switch

General specifications



Product Name	Catalog Number
Eaton Bussmann series RD non-fused rotary disconnect switch	RD63-3-508
	UPC
	051712402590
Product Length/Depth	Product Height
2.7 in	2.97 in
Product Width	Product Weight
2.55 in	0.59 lb
Warranty	Compliances
Not Applicable	Not Applicable
	RoHS Compliant

Electrical rating

Amperage Rating

63A

Voltage rating

600 V

Physical details

Operating temperature - max

70 °C

Operating temperature - min

-20 °C

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[RD63-3-508~Switch 63A Non-F 3P UL508](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - RD63-3-508](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)