



PRODUCT-DETAILS

S16/50M

16MM GS CONDUIT 50M - MET



General Information	
Extended Product Type:	S16/50M
Product ID:	7TCA296010R0040
EAN:	5020963001277
Catalog Description:	16MM GS CONDUIT 50M - MET
Long Description:	Inherent Low Fire Hazard Steel Conduit, 3/8 Inch, Nominal Conduit Size 16mm, Outside Diameter 16.0mm, Inside Diameter 13.0mm, Static Bend Radius 35mm, Reel Length 50 Meters, Galvanised Steel General Purpose
Display Name:	S16/50M

Additional Information	
Product Main Type:	Adaptaflex Flexible Cable Protection
Application:	Indoors / Outdoors - Light Industrial, Buildings

Ordering	
EAN:	5020963001277

UPC: 786210261430

Dimensions

Outside Diameter: 16.0 mm

Technical

Number of Batteries: 0

Material: Galvanized Steel

Environmental

WEEE Category: Product Not in WEEE Scope

RoHS Information: Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units: 1 piece

Package Level 1 EAN: 5020963001277

Package Level 1 Height: 5 in
127 mm

Package Level 1 Depth / Length: 16 in
406 mm

Package Level 1 Width: 16 in
406 mm

Certificates and Declarations

Declaration of Conformity - CE: 9AKK107492A9618

RoHS Declaration: 9AKK107992A8994

REACH Declaration: 9AKK107992A8994

External Classifications and Standards

ETIM 8: EC001179 - Protective metallic hose

ETIM 9: EC001179 - Protective metallic hose

UNSPSC: 39131706

Categories

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

