

Datasheet

ECP-6 UK series

6W plug-in power supply



Features

- x No load power consumption
- x Protections: short circuit//overload voltage//overload current
- x UK and European versions available
- x Compact and light-weight
- x Withstands operating environment of 0-40°C
- x Efficiencies up to 86%
- x 3 year warranty
- x External switch mode plug-top power supplies
- x Efficiency level V, Conforms to Energy-related Product Directive 2009/125/EC
- x Energy saving power supply
- x Class II double insulated
- x 1.2 metre (approx.) output lead with 2.1x5.5x9.5mm centre positive output connector
- x Regulated output
- x EMC compliance to EN 55022 Class B

Part number	Voltage	Rated current	Voltage range	Rated power	MTBF
726-2690	5V	1.2A	4.7 ~ 5.3V	6W	100,000hrs min. MIL-HDBK – 217F (25°C)
726-2700	7.5V	0.8A	7.1 ~ 7.9V		
726-2703	9V	0.67A	8.5 ~ 9.5V		
726-2707	12V	0.5A	11.4 ~ 12.6V		
726-2716	15V	0.4A	14.25 ~ 15.75V		
726-2719	18V	0.33A	17.1 ~ 18.9V		
726-2713	24V	0.25A	22.8 ~ 25.2V		

Mechanical specification

