

Mini Workshops

- Ideal as a standalone maintenance, quality or tool setting station remote from the main area
- Welded steel construction with reinforced doors
- Galvanised shelves with 60kg U.D.L. capacity
- Multiplex wooden worktop
- Roller bearing drawers with 60kg U.D.L. capacity
- Internal panels in perfo and louvre styles
- Optional hook, bin and divider kits
- All models 1050mm Wide x 550mm deep x 2000mm high



Tools and accessories shown are not included.

bott verso is also available with RAL7035 light grey (shown), RAL3004 red, or RAL7016 anthracite fronts / doors.

Model Shown with optional hook and bin kits.



A



B



C

Model	Shelves	Drawers	Panels	Worktop	Order Ref.	Price £
A	-	4x 125mm, 2x 175mm	1x perfo, 1x louvre	1	16926573.11	951.66
	1	1x 100mm, 1x 125mm, 1x 175mm	1x perfo, 1x louvre	1	16926572.11	725.21
B	1	2x 125mm	1x perfo, 1x louvre	1	16926571.11	660.59
C	2	1x 175mm	1x perfo, 1x louvre	1	16926570.11	634.64

Housing:

RAL 7035 – light grey

Fronts:

RAL 5010 – gentian blue .11

RAL 7035 – light grey .16

RAL 3004 – crimson red .24

RAL 7016 – anthracite grey .19

- cupboards
- mobile
- dividers
- cupboards
- benches
- perfo
- cnc
- cupboards
- mobile
- verso cupboards**
- benches
- facilities
- cases & seating