

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts




Customers Also Bought



TE Part #625250-000
D-128-0008



TE Part #1-2176558-9
3430 B2 1% 5R1 100ppm 1k RL



TE Part #2-2176558-4
3430 B2 1% 8R2 100ppm 1k RL



TE Part #1-1991226-2
1 POS. RING TONGUE HOUSING
ASSY. IPT 16-



TE Part #2141155-3
PROTEC. COVER 8MM HV,90DEG



TE Part #1-2141227-2
2POS,PIN DIA 8.0,PIN HSG,ASSY,SLD



TE Part #2141630-1
5POS,HVA630,REC HSG ASSY,
180DEG,HVIL



TE Part #2141809-3
CONTACT KIT, BODY AND SPRING,



TE Part #3-2177380-1
RING TONGUE, CONTACT



TE Part #1-2310922-1
2POS,8MM HV,REC HSG,90D,ASSY,
SEALED,V0,

Documents

Product Drawings

FINGER PROT CAP 8MM HV,90DEG

German

CAD Files

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2141159-1_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2141159-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2141159-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

English