

Single-LED super bright

10-2413.1132R

Distribution by
Rs-online



<https://rs-online.eao.com/p/10-2413.1132R>

Your product:



10-2413.1132R

Single-LED super bright

OPERATING-/INDICATION PART

Illumination colour: Red

ELECTRICAL CHARACTERISTICS

Operating voltage: 28 V AC/DC +10%

Operation current: 14 mA $\pm$ 15 %

Lumi. Intensity: 7700 mcd

MECHANICAL CHARACTERISTIC

Weight: 0.002 kg

CERTIFICATE

REACH: REACH compliant

RoHS: RoHS compliant

OTHER


Short Description: Single-LED super bright, BA9s, Red, 28 V AC/DC +10%

Kind of illumination: Single_LED super bright


Product attributes: The max. overall length of the lamp may not exceed 25mm

Hints: The specified 12, 24, 28, 48 VAC/DC versions are built with a bridge rectifier. Electrical and optical data are measured at 25 °C. Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED

Wiring diagrams:



Dimension drawings:



A = (standard)
B = (super bright)