



## Main

|                           |                                     |
|---------------------------|-------------------------------------|
| Range of product          | Series 56                           |
| Range                     | Clipsal - 56 Series                 |
| Product brand             | Clipsal                             |
| Product or component type | Switch                              |
| Device presentation       | Basic element with full cover plate |
| Device application        | Control                             |
| Colour                    | Cover: grey                         |
| Handle colour             | Grey                                |
| Suitability for isolation | Yes                                 |

## Complementary

|                                |                    |
|--------------------------------|--------------------|
| Switch function                | 1-pole             |
| Poles description              | 1P                 |
| Actuator                       | Key                |
| Control type                   | Rotary knob        |
| Number of poles                | 1                  |
| Device mounting                | Surface            |
| Fixing mode                    | By screws          |
| Material                       | PC (polycarbonate) |
| Tightening torque              | 0.8 N.m            |
| Local signalling               | without            |
| [Ue] rated operational voltage | 250 V AC 50 Hz     |
| Rated current                  | 20 A               |
| Breaking capacity              | 20 kA              |
| Motor M-rating AS3133          | M250 at 250 V      |
| Rotary handle padlocking       | 2 padlocks 8 mm    |
| Marking                        | ON-OFF             |
| Marking location               | Marking on surface |
| Height                         | 107 mm             |
| Width                          | 101 mm             |
| Depth                          | 112 mm             |
| Net weight                     | 0.596 kg           |
| Targeted country               | Australia          |

## Environment

|                                       |                             |
|---------------------------------------|-----------------------------|
| Ambient air temperature for operation | -25...75 °C                 |
| IP degree of protection               | IP66 conforming to AS 60529 |
| Standards                             | AS/NZS 3133                 |

## Packing Units

|                              |            |
|------------------------------|------------|
| Unit Type of Package 1       | PCE        |
| Number of Units in Package 1 | 1          |
| Package 1 Weight             | 587 g      |
| Package 1 Height             | 112.5 mm   |
| Package 1 width              | 112.5 mm   |
| Package 1 Length             | 106.5 mm   |
| Unit Type of Package 2       | CAR        |
| Number of Units in Package 2 | 12         |
| Package 2 Weight             | 7.152 kg   |
| Package 2 Height             | 250 mm     |
| Package 2 width              | 214 mm     |
| Package 2 Length             | 338 mm     |
| Unit Type of Package 3       | PAL        |
| Number of Units in Package 3 | 768        |
| Package 3 Weight             | 457.728 kg |

## Offer Sustainability

|                            |                                                                                                                                   |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                             |
| REACH Regulation           |  <a href="#">REACH Declaration</a>               |
| EU RoHS Directive          | Compliant  <a href="#">EU RoHS Declaration</a>   |
| Mercury free               | Yes                                                                                                                               |
| RoHS exemption information |  <a href="#">Yes</a>                            |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a>        |
| Environmental Disclosure   |  <a href="#">Product Environmental Profile</a> |