




RS Pro M12 Panel Mount Male 8W 200mm, PG9

RS Stock No: 144-7611





All dimensions are in mm.

General Specification Rated Operational Voltage 30 V Current Rating 2A Insulation Resistance >= 100 M Ω Temperature Range -25°C ... +75°C Degree of Protection IP67

3 GREEN	2 BROWN
	1 WHITE
4 YELLOW	8 RED
5 GREY	7 BLUE
	6 PINK

Pin Assignment

Material Specification	
Housing Material	Brass Ni Plated
Contact	Cu-Zn
Contact Plating	Gold Plated
Contact Carrier	Nylon 66
O-Ring	Neoprene
Pole	8
Clamp Nut	PG9

Cable Specification	
Cross Section of Wire	0.25 sq.mm
Termination	Partially Stripped
Cable length	200 mm