

FEATURES

- This RS PRO rackmount enclosure is made from high-grade cold-rolled steel, with the front and back panels made from lightweight aluminium
- Each unit offers top, base and side ventilation apertures for optimum cooling, especially when housing electronic equipment or components
- The two-layer front panel has been designed with an adjustable gap (0 – 20 mm)
- The whole enclosure unit is powder-coated following a 5-stage iron phosphate pre-treatment to prevent oxidation and provide longer-lasting protection, especially in harsh environments
- The precise design and high-quality manufacturing standard enables fast and easy assembly while offering complete compatibility with all 19-inch standard equipment
- In addition to this, each unit has 2 extruded aluminium handles and 4 adhesive rubber feet for additional versatility across a wide range of applications
- Gloss black finish for easy cleaning and keeping the surface dust and debris free
- The enclosure unit and accessories supplied with the unit are packed flat for convenient shipment and storage
- Supplied with 4 fitted and 4 loose Board / Chassis plate / Component fixing crossbars
- The PF19 enclosure range is available in a wide variety of sizes

RS PRO Rackmount Enclosures - Ventilated Rackmount Enclosure

RS Stock No.: 665-7700



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO PF19 Series Rackmount Enclosure

Introducing the RS PRO PF19 Rackmount Enclosures, a high quality and heavy-duty electronic enclosure series, suitable for a wide range of uses. Constructed from a mixture of high grade rolled steel and lightweight aluminium panels, these rackmount enclosures offer a sturdy construction and combined with the tough powder-coated finish, provide long-lasting life of the product even in harsh environments. The enclosures are easy to use and assemble, thanks to the precision workmanship and well-engineered design. In addition to this, the high-quality materials that are used to manufacture this RS PRO enclosure offer a strong and aesthetically-pleasing finished product, suitable for a wide range of applications both at home or in industry.

General Specifications

Series	PF-19
Mounting	Rackmount
Rack Units	1U
Material	Steel
Horizontal Pitch	84 HP
Ventilated	Yes
Handles	Yes
Colour	Black
For Use With	Provide long-lasting life of the product even in harsh environments
Features	Each unit offers top, base and side ventilation apertures for optimum cooling
Sound Proof	No
Fan Included	No

Mechanical Specifications

Dimension	43.7 x 482.6 x 245mm
Height	43.7mm
Depth	245mm
Width	482.6mm

Approvals

Declarations	RoHS Certificate of Compliance
Standards Met	IEC 297 EIA RS-310 C1977 DIN 41494 Conforms to ASTM D610-01 (Creepage test) Conforms to ASTM B117 (500 hours salt spray test)

Similar Products

Stock No.	Brand	Product Name	Material	Dimension	Rack Units
6657700	RS PRO	Ventilated Rackmount Enclosure	Steel	43.7 x 482.6 x 245mm	1U
6657712	RS PRO	Ventilated Rackmount Enclosure	Steel	88.1 x 482.6 x 335mm	2U

Accessories / Dimension Drawing / Top View / Front View / Side View

There are 24 different sizes and configurations which are available in :

- Height : 1.5U to 6U (B)
- Width : 482 (A)
- Depth : 90, 245, 335, 425 and 465 (D)

