



devolo WiFi Repeater

Technical data

Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3x, IEEE 802.11 b, g, n (2,4 GHz Single Band) Auto MDI/X
Transmission speeds	Ethernet 10/100 (mbps) Wi-Fi 300 (mbps, 2x2 MIMO)
Modulation • Carrier	Wi-Fi DSSS (IEEE 802.11b) • Wi-Fi OFDM (IEEE 802.11g, n) • Wi-Fi 13
Security	WPA/WPA2 WPS PBC
LEDs	Wi-Fi
Buttons	WPS
Socket • Connector • Countries	Type G (BS 1363) • (none) • (UK)
Device port	1 x Ethernet RJ45 2 x Antenna
Power consumption	Maximum W/A: 3,9 / 0,1 Typical W/A: 3 / 0,1 Stand-By W/A: -
Power supply	internal 100-250 V AC 50-60 Hz
Temperature (Storage • Operating)	-25°C to 70°C • 0°C to 40°C
Dimensions (in mm, without plug)	105(L) x 58(W) x 42(H)
Ambient conditions	10-90% Humidity (non-condensing)
Operating systems	Windows 7 (32 Bit), Windows 7 (64 Bit) Windows 8.x (32 Bit), Windows 8.x (64 Bit), Windows 8.x Pro (32 Bit), Windows 8.x Pro (64 Bit) Ubuntu-Linux 14.04 (32 Bit), Ubuntu-Linux 14.04 (64 Bit), Ubuntu-Linux 15.04 (32 Bit) Ubuntu-Linux 15.10 (64 Bit), MAC OS X 10.6, MAC OS X 10.7, MAC OS X 10.8, MAC OS X 10.9 Android 2.3, Android 4.0, Android 4.1/4.2, Android 4.4 iOS 7, iOS 8
Certifications	CE Class B (EU, CH, NO)



devolo WiFi Repeater

Sales information

Warranty (in years)	3
Accessories	Printed Install Flyer

Single adapter

9423 (UK)

EAN: 4250059694231
Weight: 250 g
Dimensions: 115 x 190 x 81 mm

WEEE additional information:

Weight WEEE: 115 g
Paper (Green Dot): 115 g
Plastic (Green Dot): 4 g
other (Green Dot): 0 g