



| Part Number | Impeller Number | Mixed-Flo Number | Max. Dimensions (inches) | | |
|--------------|----------------------------------|------------------|--------------------------|----------------|---------------|
| | | | a | b | c |
| 9566-2-4013 | 133 | | 5.08 (129) | 3.43 (87) | 0.51 (13) |
| 9588-2-4013 | 175, 180 & 190 | | 7.28 (185) | 5.12 (130) | 0.67 (17) |
| 9609-2-4013 | 220 | | 9.96 (253) | 6.10 (155) | 0.79 (20) |
| 9597-2-4013 | R1G225 R4E225-AR R2E225-BB | | 8.27 (210) | 5.87 (149) | 1.10 (28) |
| 9607-2-4013 | R4S225 R4E225-AC 250 | | 8.78 (223) | 6.57 (167) | 0.87 (22) |
| 9614-2-4013 | 280 | | 10.04 (255) | 7.40 (188) | 0.98 (25) |
| 9621-2-4013 | 310 | | 11.81 (300) | 7.60 (193) | 1.69 (43) |
| 51357-2-4013 | 355 | | 13.78 (350) | 8.90 (226) | 2.36 (60) |
| IR/265497 | RH28M | | 10.43 (265) | 7.09 (180) | 1.69 (43) |
| IR/265498 | RH31M | | 11.81 (300) | 7.56 (192) | 2.09 (53) |
| IR/265499 | RH35M | | 13.19 (335) | 8.98 (228) | 2.28 (58) |
| IR/265500 | RH40M | RM35D | 14.72 (374) | 10.12 (257) | 2.60 (66) |
| IR/265501 | RH45M | RM40D | 15.94 (405) | 11.38 (289) | 2.80 (71) |
| IR/265502 | RH50M | RM45D | 17.72 (450) | 12.80 (325) | 3.11 (79) |
| IR/265503 | RH56M | RM50D | 19.88 (505) | 14.33 (364) | 3.43 (87) |
| IR/265504 | RH63M | RM56D | 22.05 (560) | 16.14 (410) | 3.74 (95) |
| IR/265505 | RH71M | | 25.00 (635) | 18.11 (460) | 4.17 (106) |