



Main

Range	Linergy
Product name	BW
Product or component type	Busbar support
Device short name	LA9Z
Quantity per set	Set of 10






Complementary

Range compatibility	TeSys
Poles description	3P
Permissible current	630 A - busbar cross section: 30 x 10 mm 150 A - busbar cross section: 12 x 5 mm 362 A - busbar cross section: 20 x 5 mm 500 A - busbar cross section: 30 x 5 mm 300 A - busbar cross section: 12 x 10 mm 564 A - busbar cross section: 20 x 10 mm
[Ui] rated insulation voltage	690 V conforming to IEC 60947-1 690 V conforming to NF C 20-040
Distance between supports	400 Mm busbar 12 mm height 800 Mm busbar 20 mm height 800 mm busbar 30 mm height
Busbar pitch	60 mm
Colour	Grey

Environment

IP degree of protection	IP20 with protective cover
Temperature resistance	125 °C
Standards	IEC 61439-2 UL 508
Product certifications	UL

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile