



Datasheet

RS Pro 2 Hole Flange Mount Plug 30A Circular Connector 21mm (Threaded) IP68 for Solder Termination

RS Stock No: 131-6379



Product Details

From RS Pro, these 2 hole flange mount connector plugs with threaded coupling are serious contenders for your high current industrial application. The high-quality circular connectors have a bigger and stronger shell. Certified with a waterproof IP68 rating, they excel in harsh environments.

The 2 hole flange mount connectors can be used with cable connector sockets for cable-to-panel mount connections.

Material and Specifications:

Product Type	Connector	Overmolded cable Assemblies	
Coupling	Threaded Coupling	Threaded Coupling	
Shell Material	Nylon66, Fire resistance: V-0	PC,PVC,Fire Resistence:V- 0, Locking nut Material:Anodized Aluminum	
Insert Material	PPS Max Temperature 260C Fire resistance: V-	PPS Max Temperature	
	0	260C Fire resistance: V-0	
Contact Material	Brass with Gold plating	Brass with Gold plating	
Termination	SP13:Solder, SP17:Solder/Crimp,SP21:solder/screw/crimp		
	SP13 I: 4-6.5mm, SP13 II: 5-8,mm		
Cable outer Diameter	SP17: 6-10mm		
Range	SP21 I: 4.5-7mm SP21 II:7-12mm		
IP Rating	IP68	IP66	
Mating Cycle	>500	>500	
Temperature Range	-25C~+85C	-20C~+85C	
Insulation Resistance	2000	2000	



Contact Arrangement and Spec for Solder/Screw:

Number of Contact	2	3	4	5	5B
Male Contact Face view		2 0 1	01 3 0 0 2 04	2 0 1 4 0 3 5	2 1 4 0 0 4 0 3
Rated Current(A)	30A	30A	30A	30A	5A, 30A
Contact Diameter	Ø 3X2	Ø 3X3	Ø 3X4	Ø3X5	Ø 1X3 Ø 3X2
Termination	solder / screw	solder / screw	solder / screw	solder / screw	solder / screw
Rated Voltage (AC.V)	500V	500V	500V	500V	500V
Test Voltage (AC.V) 1min	1500V	1500V	1500V	1500V	1500V
Contact Resistance m	1	1	1	1	5,1
Wire Sizemm2/AWG	≤4.17/11	≤4.17/11	≤4.17/11	≤4.17/11	≤0. 785/18 ≤4.17/11