

OEL24-1



Sample image

Order symbol : OEL24-1

Product nr : 2550000

Description : Modular component enclosure, grey screw cover with inspection window, 2x13 modules

EAN : 6418074300546

El. number :

- Finland : 3424796
- Denmark : 8212010644
- Sweden : 2507762

Dimensions :	Height	Width	Depth
mm :	280	280	160
inch :	11.02	11.02	6.3

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	Clear transparent
Gasket material :	Polyurethane

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP65;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Not insulated
UV resistance :	-
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C