

Datasheet

RS 2 pairs , 350m CW1411 Telecom Cable Black Sheath, 3 Strands

Stock Number - 411-813



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):A:300



Construction:

A:

Conductor: Bare Copper

Conductor Dia. (mm): 0.5 ± 0.01

B:

Conductor: Steel coated with brass diameter

Conductor Dia. (mm): $0.25 \pm 0.008 \times 3$

A:

Insulation: HDPE

Insulation Dia. (mm): $1.02 \pm 0.05 \times 2C$

Twist x 2P

B:

Insulation: PVC

Insulation Dia. (mm): $1.0 \pm 0.05 \times 3C T$

Tape: Mylar Sprial

A rip cord : Nylon

ID Thread

Jacket: HDPE

Outer Dia. (mm): 5.4 ± 0.15

Colour:

The colour of the insulation:

A: White , Orange ; Black , Green

B: Yellow x 3

The colour of the Jacket: Black

Marking(3times/m):

RS 411813 External 2 pair dropwire 10B

CW1411

Performance:**Electrical Characteristics:**

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<95

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :
>10000

Mutual Capacitance (nF/km) : <56

Capacitance Unbalance (pF/500m) : <275

Breaking load :

Min. : 1350N

Max.: 1550N

