



greenpar 1-1337427-0

(Tyco Electronics P/N: 1-1337427-0)

Searchable Features:

Brand:	Greenpar
Government/Industry Qualification:	No
Connector Type:	BNC
Product Type:	Connector
Gender:	Plug
Terminate To:	Coaxial Cable
Coaxial Cable Termination Type:	Crimp
Crimp Type:	Hex
Coaxial Cable Type (RG/U or Mfg.):	141A/U, 58C/U, Raychem 5021D1331, Raychem 5021D1831, Raychem 5021M1631, Raychem EPD 71169Q, URM 43, URM 76
Body Style:	Straight
Surface Mount:	No
Grade:	Professional
Connector Impedance:	50
Panel Attachment:	No
Center Contact Material:	Brass
Center Contact Plating:	Silver
Body Material:	Brass
Body Plating:	Silver
Sealed:	No
Isolated:	No
Dielectric Material:	PTFE
Coupling Nut Material:	Brass
Packaging Method:	Individual
Polarized:	No

Other Properties:

Military Style Number:	UG-1785/U
Packaging Quantity:	50
Ferrule Type:	Hex
Hand Tool No.:	9-1478240-0
Interchangeable Die Set Number:	9-1478242-0
Crimp Dimensions:	1.75 + 2.6 + 5.6 + 6.5
Operating Temperature (Max.) (°C):	165
Frequency:	DC to 4 GHz
Gasket Material:	White Silicone Rubber