



ENGLISH

European 2-Pin Plug-in top Power Supply 12vdc 60watt



The RS Pro Range of Class II 60watt AC/DC European plug-in power supplies provide 60 watts of continuous power in a compact fixed wall plug enclosure suitable for use in many general power applications.

Features:

- European Fixed AC Head
- 3 Year Warranty
- Level VI Efficiency
- CE Approved





ENGLISH

Specification	
RS Stock Number	1753331
Input Voltage Range	90-264Vac
Input Frequency Range	47-63Hz
Input Current Rated	1.5A Max
Output Voltage Rating	+12V
Output Current Range	4A
Output Min Current	0.0A
Output Connection Type	2.1x5.5x12mm Centre Positive – Straight
Total Output Regulation	+/- 5%
Line and Load Regulation	+/- 1%
Ripple & Noise	200mVp-p
Efficiency	88% Min
Over Voltage Protection	Auto Recovery
Over Load Protection	Auto Recovery
Operating Temperature	0 to 40°C
Storage Temperature	-20 to +80°C
Operating Humidity	10 to 90%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	CE(EN60950-1)
EMI Standard	EN55032 EN61000-3-2
MTBF	50k Hours
Size mm max.	117 (L) 51 (W) * 33.5(H)
Weight	280 g
Regulator Type	Switched Mode Power Supply