
You can view this page in:

EN DE SV FI CS DA EL ES FR HU IT JA KO NL NO PL PT RU SK
TR ZH

Detailed information for: TC5349A-TB

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

TC5349A-TB

General Information

Extended Product Type:	TC5349A-TB
Product ID:	7TCG009890R0001
EAN:	5414363059011
Catalog Description:	LATCHG CLAMP .98X.98IN NAT NY ADH
Long Description:	Re-Usable Latching Cable Clamp, Natural Nylon 6.6 for Temperatures up to 85 Degrees Celsius (185 F), Length of 25.0mm (0.984 Inches), Width of 25.0mm (0.984 Inches), Maximum Height of 14.5mm (0.57 Inches), Screw Mounting Method, Mounting Hole Diameter of 4.3mm (0.17 Inches), 100 Pack

Categories

Products » [Low Voltage Products and Systems](#) » [Installation Products](#) » [Wire Management and Connectivity](#) » [Cable Ties](#)

Ordering

EAN:	5414363059011
UPC:	786210804941

Container Information

Package Level 1 Units:	100 piece
Package Level 2 Units:	1000 piece
Package Level 2 Width:	11.4 in 290 mm
Package Level 2 Height:	9.1 in 231 mm
Package Level 2 Depth / Length:	15 in 381 mm

Additional Information

Brand / Label:	Ty-Rap
Color:	Natural
Effective Date:	19930115
Material:	Nylon/Polyamide 6.6
Mounting Type:	Adhesive
Number of Batteries:	0
Process Temperature Rating:	-40 to +185 °F
Product Name:	OTHER PLASTIC ITESM
Product Type:	Mounting Base
Special Functions:	Integral top cover incorporates a unique ratchet design that is fully adjustable and releasable.

Certificates and Declarations (Document Number)

Data Sheet, Technical Information: TC5349A-TB

Instructions and Manuals: TC5349A-TB

Classifications

ETIM 6:	EC000449 - Mounting base and -element for cable ties
ETIM 7:	EC000449 - Mounting base and -element for cable ties
UNSPSC:	39121717
WEEE Category:	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC):	5065 >> Cable tie mounts



© Copyright 2022 ABB