

Busch-Dimmer®
Flush-mounted devices
Busch-Dimmer® insert



With rotary control, soft-catch and with trailing edge control.
For incandescent lamps, 230 V tungsten halogen lamps and low-voltage halogen lamps with electronic transformers.
Low-noise, short-circuit-proof, overload-protected.
Without cover plate.

Rated voltage: 230 V~, +10 % / -10 %, Rated frequency: 50 Hz,
Rated power: 40 - 420 W/VA

Not suitable with conventional transformers., Illuminable with neon lamp. Neon lamp included in delivery with cover plate., In case of electronic transformers, 5 % transformer losses., Provided with terminal for net disconnection devices., Also applicable for 1gang 2way installations., ./.

Order Code : 6513-0-0586
Article No. : 6513 U-102-500
EAN: 4011395037256