



Hoja de información del producto

## LUHR 12



Unidad de rodamiento lineal sin retenes



LUHR  
With double lip seal



LUHR  
With shaft seals



A [mm]:	28
D = Da [mm]:	19
Fw [mm]:	12
H [mm]:	17
H1 [mm]:	33
H2 [mm]:	16
H3 [mm]:	11
J [mm]:	29
L [mm]:	40
N [mm]:	4.3
N1:	M5
Hileras de bolas [#]:	5
Cdyn [N]:	695

Fecha: 21/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

Hoja de información del producto

## LUHR 12

Unidad de rodamiento lineal sin retenes

CO [N]:	510
Peso [kg]:	0.08
A1[mm]:	35
C1[mm]:	34

**Fecha:** 21/05/2020

The contents of this report are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this report but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.