

FEATURES

- **Flexible design:** Easily adapts to different surfaces and shapes for versatile installation
- **IP54 rating:** Offers protection against dust and splashes, suitable for indoor and semi-outdoor use
- **Green LED colour:** Provides vibrant and distinct lighting for decorative purposes
- **16.6 mm LED pitch:** Ensures consistent light distribution along the strip
- **60 LEDs per metre:** Delivers bright and uniform illumination
- **4.8 W/m power consumption:** Energy-efficient operation, reducing electricity costs
- **290 lm/m luminous flux:** Offers sufficient brightness for various applications
- **24 V DC voltage:** Compatible with standard power supplies for easy integration

RS PRO Flexible LED Strip Light, Green, 5 m

RS Stock No: 558-400



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible LED strip light offers a versatile lighting solution for various applications. With a vibrant green hue, it is ideal for decorative and functional lighting setups. Its flexibility allows for easy installation in a variety of settings, providing efficient illumination with a power consumption of 4.8 W/m.

General Specifications

| | |
|------------------------------|-----------------|
| Flexible/Rigid | Flexible |
| LED Colour | Green |
| LED Pitch | 16.6 mm |
| Number of LEDs Per Metre | 60 |
| Product Type | LED Strip Light |
| Typical Luminous Flux (lm/m) | 290 lm/m |

Protection Category

| | |
|-----------|------|
| IP Rating | IP54 |
|-----------|------|

Electrical Specifications

| | |
|-----------------|---------|
| Power Per Metre | 4.8 W/m |
| Voltage | 24 V dc |

Approvals

| | |
|---------------------|----------|
| Standards/Approvals | CE, RoHS |
|---------------------|----------|

Mechanical Specifications

| | |
|--------------|------|
| Strip Length | 5 m |
| Strip Width | 8 mm |

