



PRODUCT NUMBER: 6246158
BACOU CREEK AMG S3 CI
SRC

Water resistant oiled leather & textile panels shoe. PU2D outsole injected. SRC certified. 200J Spacium™ toe cap in injected polymer. Flexium™ anti-puncture sole. Complies with EN ISO 20345:2011 standard.

Honeywell

Overview

Reference Number

6246158

Product Type

Footwear

Range

Bacou Original Free

Brand

Honeywell

Brand formerly known as

BACOU

Industry

- Building and Construction
- General Industry
- Logistics
- Maintenance
- Transportation
- Utilities

Product Use

- Safety shoes for professional use.

Features & Benefits

Feature

EN ISO 20345:2011 certified. SRC certified.

Benefit

Ensures better protection.

Feature

Water resistant oiled leather & textile panels shoe.

Benefit

Resistant to tearing and spattering of fluids: extended life cycle

Feature

Poromax® lining

Benefit

Breathable, 3D absorbent & quick-dry interior lining

Feature

Reinforced protection at the front and back

Benefit

Improved resistance and protection

Feature

Flexium™ anti-puncture midsole: non-metallic, made with high tenacity textile fibres

Benefit

The midsole is light and flexible. No constraints for the wearer when flexing the foot

Feature

Lateral watertight bellows

Benefit

Prevents liquid and dust from entering the shoe

Feature

Padded ankle collar and tongue

Benefit

Adapts to the user's foot shape, ensures comfort when worn for long periods

Technical Description

Sizes

EU: 35 - 49 / UK: 3 - 13.5

Table Size

table_size_2749_id_2576

Midsole

Flexium™ anti-puncture midsole in high tenacity textile.

Upper

Water resistant oiled leather & textile panels shoe. Reinforced protection at the front and back. Poromax® lining with 3D antibacterial and antimicrobial structure. Lateral watertight bellows. Padded ankle collar and tongue.

Toe Cap

200J SPACIUM™ toe cap in injected polymer. Non-metallic: 50% lighter than steel. Extra-wide for greater comfort: suits all foot types. Non magnetic. Thermal insulator. Unalterable.

Insole

Dual density PU foam for intensive use. Removeable for easy care. Antibacterial for a longer life span and to prevent odour. Antistatic for optimal efficiency. Comfortable heel pads. Evacuation channels. The Bacou X'Max Black Insole (ref 6000350) can be sold separately. Available from 1 unit (by pair) in an individual packaging

Outsole

Dual density polyurethane: PU 2D. Comfort layer of density: 0.5 (guarantees lightness and flexibility, ensures shock absorption and protects against changes in temperature). Outsole layer of density: 1 (resistance to abrasion, fuel oil and grease). High slip resistance due to well defined cleat design, wide, deep and self-cleaning. SRC certified: SRA: on ceramic plates: flat 0,45 (minimum standard: 0,32) heel 0,46 (minimum standard: 0,28) / SRB: on steel floor: flat 0,24 (minimum standard: 0,18) heel 0,24 (minimum standard: 0,13). Energy absorption capacity > 20 joules. Excellent resistance to abrasion: volume loss < 150 mm³ (with a load of 10 N = 1 kg). Extension before tearing: 650%. Optimised resistance to repeated flexing > 60,000 (standard >30,000). Resistant to acids and alkalis: limited to low concentrations

Additional Features

- CI
- SRC

Certifications

 E.C. Declaration of Conformity

EC Category PPE

2

Quality Assurance

ISO 9001 / 2008

EC Certificate Number

0075/797/161/04/12/0262 ext 30/09/12

EC Attestation

 EC Attestation

REACH

EU Regulation 1907/2006 (REACH) Compliance

The substance(s) listed below may be contained in this product above the threshold level of 0.1% by weight of the listed article.

Product Reference Sold in Europe	Substance > 0.1%
Substance Name	CAS Number
No Substance Content	

Additional Information

User Manual

User Instruction EN ISO 20345 2011-Footwear-Honeywell-032012

Maintenance

Life Cycle

- We advise that the footwear should be used in the limit of 3 years following the manufacturing date, which figures on the footwear.
- After this time limit, certain factors such as: exposure to sunlight, hydrometry, temperature changes, could cause a modification in the structure of the material, which would no longer maintain the same performance levels with regards to the requirements defined in the European Directive 89.686 CEE.

Storage Information

- Footwear should be stored in their original packaging, kept in a controlled stock area, not subject to rapid changes in temperature or humidity levels.

Care Instructions

- After use leave your footwear to dry in an aired place away from heat. Remove any excess dust or dirt with a brush. Remove any marks using a damp cloth and soap if necessary.
- Finally polish any grain or pigmented leathers using a commercially available shoe care product.



En exécution de la Directive 89/686/CEE du 21 décembre 1989 concernant le rapprochement des législations des états membres relatives aux équipements de protection individuelle et des décrets n° 92-765, 766 et 768 du 29 juillet 1992 portant transposition de cette directive en droit français,

In application of the Directive ref. 89/686/EEC of 21st December 1989, concerning the alignment of member state legislation relating to personal protective equipment and the decrees n° 92-765, 766 and 768 of the 29th July 1992 concerning the transposition of the Directive into French law,

CTC

habilité par arrêté du Ministère du Travail, de l'Emploi et de la Santé du 20 décembre 2010,
authorized by decree of the Ministry of Work, Employment and Health of December 20th, 2010,

identifié sous le numéro 0075, publié au JOCE, attribue :

identified by the number 0075, published in the Official Journal of the European Community, delivers:

L'ATTESTATION D'EXAMEN CE DE TYPE
CE TYPE EXAMINATION CERTIFICATE
N°0075/797/161/04/12/0262 – EXT 30/09/12

Au modèle d'équipement de protection individuelle suivant :

to the following model of personal protective equipment:

- **chaussure de sécurité à usage professionnel,**
safety footwear for professional use,
- **référence et nom du modèle : 6246158 - BACOU CREEK AMG S3 CI SRC**
reference and name:
- **responsable de la mise sur le marché :**
applicant of the CE type examination certificate:

HONEYWELL SAFETY PRODUCTS EUROPE
ZI PARIS NORD II
33 Rue des Vanesses
BP 55287 VILLEPINTE
95958 ROISSY CHARLES DE GAULLE
FRANCE

Le modèle **6246158 - BACOU CREEK AMG S3 CI SRC** est une variante raccordée au modèle **6246157- BACOU PEAK AMG S3 CI SRC**

The safety footwear model 6246158 - BACOU CREEK AMG S3 CI SRC is considered as a variant of the reference model 6246157- BACOU PEAK AMG S3 CI SRC

Les niveaux de performance et de sécurité sont identiques à ceux du modèle de raccordement, ainsi que les marquages, à l'exception du code article.

Safety levels offered are the same for both the reference model and its variant, just as the markings except the article code.

Fait à Lyon, le 5 septembre 2012

Drawn up in Lyon, on September 5th, 2012

Etablie par : Nadine PIPAZ

Issued by:



NOTA : Toute modification apportée au matériel neuf, objet de la présente attestation d'examen CE de type doit être portée à la connaissance de l'organisme habilité en application de l'article R. 4313-38 du Code du Travail ainsi que toute modification des informations contenues dans le dossier technique sur la base duquel l'attestation CE de type a été délivrée (changement de lieu, changement de raison sociale du fabricant, retrait de certificat d'assurance qualité...).

Any modification to new items of the personal protective equipment object of this CE type examination certificate or any modification of the information contained in the manufacturer technical file which served for the deliverance of the CE type approval certificate (change of adress, change of company status) should be brought to the attention of the notified body in accordance with law n° R. 4313-38 of the French Code of Work

Cette attestation comporte 2 pages numérotées 1/2 et 2/2.

This certificate contains 2 pages numbered in the following way 1/2 and 2/2.

CTC - 4, rue Hermann Frenkel - 69367 Lyon cedex 07 - France
Tél. : +33 (0)4 72 76 10 10 - Fax : +33 (0)4 72 76 10 00 - E-mail : ctclyon@ctcgrroupe.com
www.ctc.fr - www.ctcgrroupe.com - www.ctc-services.org

- **Gamme de pointures : 35 au 49**

Range of sizes: 40 to 47

- **Différence avec le modèle de raccordement :**

Difference with the reference model:

- **Modèle A : modèle bas**

Model A : low shoe

- **Marquages sur le produit**

Marking on the product

Chaque pied de la chaussure de sécurité est marqué de manière visible, lisible et indélébile de la façon suivante :

Each foot of the safety footwear is clearly and permanently marked with as following:

- **Marque d'identification : HONEYWELL**

logo – commercial brand

- **Marquage CE**

CE marking

- **Référence : 6246158**

reference

- **Pointure**

size

- **Mois et année de fabrication**

month and year of manufacture

- **Symboles normatifs : EN ISO 20345:2011 et S3 CI SRC**

standards symbols



E.C. Declaration of Conformity

The manufacturer or its legal representative supplier in the European Community:

Honeywell Safety Products Europe

Declares that the Personal Protective Equipment described here after conforms to the provisions of the European Council Directive 89/686/CEE:

Designation: BACOU CREEK AMG S3 CI SRC

Reference: 6246158

Standard(s): EN ISO 20345:2011

This PPE is the object of the below EC examination certificate n°:

0075/797/161/04/12/0262 ext 30/09/12

Delivered by:

Drawn up in Roissy, on the 11/06/2015

By: Ailsa Lhopital

Division: Footwear

ZI Paris Nord II 33, rue des Vanesses BP 50288 95958 Roissy CDG France

Tel: +33 (0) 49 90 79 79 Fax: +33 (0)1 49 90 79 80

www.honeywellsafety.com