## Tip Jacks Insulated Standard: Rib-Loc® Type





**Contact:** Brass body per QQ-B-626D with wrap around beryllium copper

spring per QQ-C-553

Finish: Silver

**Body:** Nylon 6/6 per ASTM D4066 **Panel Thickness:** Up to .375 (9.05)

**RATINGS** 


Current: 5 amps

**Breakdown Voltage**: 3500 Vrms minimum **Contact Resistance**: 0.005 ohms maximum

Adjacent Jack C: 1 pF nominal







## For Standard Tip Plug: .080 (2.00) Diameter FEATURES:

- · Machined contact with turret terminal
- Installs by pressing into mounting hole, no mounting hardware required
- Closed entry blocks access or probes greater than .085 (2.16)
- · Nylon UL approved for self extinguishing