

Datasheet

RS Pro Black Rubber Air Hose

Stock No: 914-5525



RS Pro range of rubber air hose is manufactured from a textile reinforced NBR/SBR synthetic rubber. Weather and ozone resistant, it is suitable for medium duty applications such as pneumatic air tools and compressors used in the construction and automotive industry and general workshop use.

Key Features:

- Abrasion, ozone and weather resistant
- Smooth rubber NBR / SBR construction
- In accordance with EN ISO 2398
- Wide temperature range -40C to +90C
- Safety factor 3:1

Application Examples:

- General workshop use
- Compressors
- Construction
- Mines
- Quarries



Specification:

RS Stock Number	Internal Diameter	External Diameter	Length	Weight per Meter	Max Working Pressure	Burst Pressure	Bend Radius
9145540	6 mm	12 mm	25 m	0.18 kg	20 bar	60 bar	60 mm
9145543	8 mm	15 mm	25 m	0.23 kg	20 bar	60 bar	80 mm
9145525	10 mm	17 mm	25 m	0.29 kg	20 bar	60 bar	100 mm
9145534	13 mm	21 mm	25 m	0.43 kg	20 bar	60 bar	130 mm
9145537	19 mm	29 mm	25 m	0.7 kg	20 bar	60 bar	190 mm
9145531	25 mm	36 mm	25 m	1.0 kg	20 bar	60 bar	250 mm