

Circuit Protection / Powerbreaker 30mA Passive RCD

RCD PowerBreaker Twin Socket Metal Pas



Technical Specification

Product Code	H22-MP
Feature 1	Type A RCD
Feature 2	Trips in less than 20mS
Feature 3	Does not need resetting after power loss
Feature 4	Dual flag system to show power on and off
Barcode	5012739646812
CE	Y
Colour	Grey
Company DUNS Number	216156018
Country of Origin	China
Current (I)	13
Degree of Protection	40
Finish body	Matt
Fixings supplied with product	Closing screws
Frequency (Hz) max	60
Frequency (Hz) min	50
Greenbrook Guarantee (Years)	3

Tel No: 01279 772 772

Email: sales@greenbrook.co.uk

Website: www.greenbrook.co.uk

HS Code	8536201090
Ingress Protection (IP)	IP40
Installation method	Surface or flush
Knock-out Dimensions	20
Knock-out Qty	9
Latching	Passive
Materials Main Body	Steel
Max Operating Current	13
Min Order Qty	1
Operating Temperature Range max C	40
Operating Temperature Range min C	-5
Package Product Max. Length (mm)	216
Package Product Max. Height (mm)	55
Package Product Max. Width (mm)	194
Package Product Weight gross (g)	592
Product (only) Max. Depth (mm)	49
Product (only) Max. Height (mm)	86.5
Product (only) Max. Width (mm)	147.5
Product Weight net (g)	522
Rated Conditional Short-Circuit Current	1500
Rated Short Circuit Breaking & Making Capacity	250
RCD Contact Break	Double pole
RCD Type	A
Sales Pack Qty	1
StatusCode	Active
Typical Trip Speed	20
UKCA	Y
Voltage (VAC) MAX (V)	240
Voltage (VAC) Min (V)	220
Voltage (VAC) Rated (V)	230
Wattage (W)	3000

Tel No: 01279 772 772

Email: sales@greenbrook.co.ukWebsite: www.greenbrook.co.uk