

Han 10 HPR Cover Toggle Locking



| Part number | 09 40 010 5401 |
|--------------------|-------------------------------------|
| Specification | Han 10 HPR Cover Toggle Locking |
| HARTING eCatalogue | https://b2b.harting.com/09400105401 |

Identification

| Category | Hoods/Housings |
|-----------------------------|---|
| Series of hoods/housings | Han [®] HPR |
| Type of hood/housing | Protection cover |
| Description of hood/housing | for bulkhead mounted housings for surface mounted housings |

Version

| Locking type | Toggle locking |
|----------------------|---|
| Size | 10 B |
| Field of application | Hoods/housings for harsh outdoor environments |

Technical characteristics

| Limiting temperature | -40 +125 °C |
|--|---------------|
| Degree of protection acc. to IEC 60529 | IP65 IP68 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| Material (hood/housing) | Aluminium die-cast Corrosion resistant |
|-------------------------|--|
| Surface (hood/housing) | Powder-coated |
| Colour (hood/housing) | RAL 9005 (jet black) |
| Material (locking) | Stainless steel |
| RoHS | compliant |



Material properties

| ELV status | compliant |
|-----------------------------|-----------|
| China RoHS | е |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |

Specifications and approvals

| Approvals | DNV GL |
|-----------|-----------------------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
| | CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| Packaging size | 1 |
|--------------------------------|--|
| Net weight | 153.2 g |
| Country of origin | Germany |
| European customs tariff number | 85389099 |
| eCl@ss | 27440208 Cap for industrial connectors |