

eco!Booster TR 045

eco!Booster with 50% more area performance than the Kärcher power nozzle; suitable for delicate surfaces. For cold and hot water high-pressure cleaners (nozzle size 045).



Order no. **2.113-087.0**

Technical data

EAN code		4066529118844
Pressure	bar	max. 300
Temperature	°C	max. 85
Nozzle size		45
Connection thread		EASY!Lock
Weight incl. packaging	kg	0.5



50% higher cleaning performance compared to the flat jet

- Thorough, fast and more sustainable cleaning.

50% higher water efficiency*

- Saves water.
- * Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

50% higher energy efficiency*

- Saves energy.
- * Based on the ability to clean 50 percent more area than a Kärcher standard flat jet with the same amount of energy and water.

COMPATIBLE MACHINES

- HD 6/13 C
- HD 7/13-4 M
- HD 8/18-4 M
- HDS 8/20 De
- HDS 8/20 G
- HDS-E 3.3/25-4 M Ec 24 kW