

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION







© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.


LOC
ESDIST
00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
A	REVISED	ECR-07-000873	16JAN07	C.Z	S.Y


4 Pos.
(SCALE 4-1)

5~15 Pos.



NOTES:


- MATERIAL: HOUSING - NYLON 66 (UL94V-0)
POST - TIN BRASS
- APPLICABLE RECEPTACLE P/N 173977
- THIS PART HAS BEEN OBSOLETED.

RECOMMENDABLE PCB LAYOUT
(PCB THK:0.8-1.6)

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

10 > * : ±0.2
30 > * > 10 : ±0.25
100 > * > 30 : ±0.3
ANGLE : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMMATERIAL
SEE NOTETOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

FINISH
SEE NOTE

DWN 31JAN03

CHK 31JAN03

S.YAO

APVD 31JAN03

T. SASAKI

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

PART NO.

Pos.

A

B

C

D

15

28

31.8

25.2

31.0

7-

-4

5-

-4

3-

-4

1-

-4

14

26

29.8

23.2

29.0

7-

-3

5-

-3

3-

-3

13

24

27.8

21.2

27.0

7-

-2

5-

-2

3-

-2

12

22

25.8

19.2

25.0

7-

-1

5-

-1

3-

-1

11

20

23.8

17.2

23.0

7-

-0

5-

-0

3-

-0

10

18

21.8

15.2

21.0

6-

-9

4-

-9

2-

-9

9

16

19.8

13.2

19.0

6-

-8

4-

-8

2-

-8

8

14

17.8

11.2

17.0

6-

-7

4-

-7

2-

-7

7

12

15.8

9.2

15.0

6-

-6

4-

-6

2-

-6

6

10

13.8

7.2

13.0

6-

-5

4-

-5

2-

-5

5

8

11.8

5.2

11.0

6-

-4

4-

-4

2-

-4

4

6

9.8

3.2

9.0

6-

-3

4-

-3

2-

-3

3

4

7.8

—

7.0

6-292253-2

4-292253-2

2-292253-2

292253-2

2

2

5.8

—

5.0

BLACK

YELLOW

BLUE

NATURAL

Tyco Electronics Corporation

SHANGHAI, CHINA

POST HEADER ASS'Y HORIZONTAL TYPE

(AMP CT CONNECTOR 2mm PITCH)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=292253

SCALE

5:1

SHEET

1

OF

1

REV

A