

6 way modular flat telephone cable



Part NO: RGW-1595
Product Code: 6 way modular flat telephone cable
Product Description

Application:
 For communication and signal control systems.


Reference Standard
 Customer's sample spec.and the general standard

Multi-construction
 6

Cable Construction

Conductor	Bare Copper
Construction	0.16±0.005x7
AWG	26
Insulation	PE
Min.Thickness	0.21
Insulation Dia.(±0.05mm)	0.95
Insulation Color	1;White; 2;Black 3; Red; 4, Green 5, Yellow; 6,Blue
Filler	Chalk
Jacket	PVC
Min.Thickness(mm)	0.66
Dia.(±0.15mm)	7.1×2.4
Jacket Color	Silver Grey(RAL9023)


Marking
No Marking
PACKAGING
 100M Coil
 8Pcs/Box



Revision History

A0-1

Design



Electrical Characteristics

Max.Conductor DC Resistance at 20°C (Ω/Km)	132
Min.Insulation DC Resistance at 20°C (MΩ *Km)	>500
Rated Temperature(°C)	-20 to +60
Rated Voltage(V)	150

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	

Label for each coil

Product label

6 way modular flat telephone cable
Silver Grey
100M
RoHS(2002/95/EC) Compliant
WW/YY

RS label

7492500
 100M
 Made in China

Date: 2011-10-12

Page: 1 / 1