



# PRODUCT DATASHEET

Datasheet creation date: 2025/05/28 10:37 (UTC)

MOTION & CONTROL  
**NSK**



## 23030CDE4

### Spherical Roller Bearings

#### Boundary Dimensions


d	150	mm	Bore diameter
D	225	mm	Outside diameter
B	56	mm	Width
r (min.)	2.1	mm	Chamfer dimension

#### Basic Load Ratings

Cr	590000	N	Basic dynamic load rating
C0r	815000	N	Basic static load rating

#### Speeds

Thermal Speed Rating (Oil-bath)	2600	min-1	Oil-bath lubrication subject to conditions outlined in ISO 15312
Mechanical (forced-circulation oil)	3600	min-1	Properly designed and controlled forced-circulation oil lubrication
Grease	1400	min-1	Grease lubrication
Oil (Oil-bath)	1800	min-1	Oil-bath lubrication



#### Abutment and Fillet Dimensions

da (min.)	162	mm	Diameter of shaft abutment
da (max.)	168	mm	Diameter of shaft abutment
Da (min.)	203	mm	Diameter of housing abutment
Da (max.)	213	mm	Diameter of housing abutment
ra (max.)	2	mm	Radius of shaft or housing fillet

#### Calculation factors

e	0.22	Constant
Y2	4.6	Axial load Factors
Y3	3.1	Axial load Factors
Y0	3	Axial load Factors

#### Mass

Mass approx.	7.9	kg	Mass approx.
--------------	-----	----	--------------

