



ENGLISH

Datasheet

## RS Pro Plain Nylon Cheese Head Machine Screws, M2 x 12mm

RS Stock No: **527-915**



### Product Details

RS Pro machine screw measuring M2 x 12 mm, is moulded from ivory coloured nylon 6.6. This cheese head machine screw features metric thread and high mechanical strength. The machine screw is ideal for use where good insulation and corrosion resistance is required. This screw is suitable for use in high voltage assemblies.

### Features and Benefits

- Metric thread
- High mechanical strength
- Ideal for use where good insulation and corrosion resistance is required
- Suitable for use in high voltage assemblies
- Moulded from ivory coloured Nylon 6.6

**Specifications:**

Drive Type	Slot
Finish	Plain
Head Shape	Cheese
Material	Nylon 66
Length	12 mm
Thread Pitch	0.4
Thread Size (Metric)	M2
Head Diameter	3.8 mm
Head Height	1.3 mm
Slot Depth	0.7 mm
Slot Width	0.7 mm