



739-8455 Data Sheet

ENGLISH

RS stock number : 739-8455
Type of tool : Mini 2" Air Angle Grinder
Power source : Compressed air
Maximum permissible operating pressure : 90 psi (6.2 bar)
Recommended operating pressure : 90 psi (6.2 bar)

739-8455

Mini 2" Air Angle Grinder

Technical Data

Features

Palm size Angle Grinder allows the operator to reach small areas
Compact and lightweight design allows maximum operator control and performance
Rear exhaust to keep airflow away from work area
High power motor for consistent performance
Ideal for smart repairers

Specifications

Disc Size: 2" / 50mm
Free Speed: 16,500RPM
Weight: 0.45kgs / 0.99lbs
Length: 4.33" / 110mm
Min Hose Size: 3/16
Air inlet thread: 1/4"
Sound: 81dBA
Vibration: 4.2m/s²
Ave Air Consumption: 1.68cfm / 48 l/min
Recommended lubrications: 10 Weight SAE Oil



Declaration of Conformity

| | |
|--|--------------------------------------|
| We | RS Components Ltd |
| declare under our sole responsibility that the | 739-8455 – Mini 2" Air Angle Grinder |
| conforms with the directive and the standards | 2006/42/EEC EN 792-6 ISO 28927 |