

ArtNo.	VE	PG	EAN
950655000	5	114	4 008224 589413



Surface Mount, Earthed socket with hinged lid, 2-fold, horizontal, without shutter, prewired, 16A, 250V~, proAQA, light-grey/dark-grey

	0.0000000	
Technical data	950655000	
Model	Protective contact	
Imprint/indication	Without imprint	
Connection type	Plug clamp	
Colour	Grey	
Colour (user defined)	grey	
Special power supply	No special power supply	
Mounting method	Surface mounted (plaster)	
Type of fastening	Mounting with screw	
Material	Plastic	
Material quality	Thermoplastic	
Surface protection	Untreated	
Surface finishing	Glossy	
Suitable for degree of protection (IP)	IP44	
Number of units	2	
With hinged lid	Yes	
With child-protection	No	
Label space/information surface	No	
Transparent	No	
Lockable	No	
Eject-mechanism	No	
With function lighting	No	
With orientation lighting	No	
Over voltage protection	No	
Fault current protection	No	
With miniature fuse	No	
Rotated central insert	No	
Nominal current	16A	
Nominal voltage	250V	
For heavy conditions (in accordance with VDE)	No	

Technical details, pictures and performance specifications given herein are only non-binding information and must not be seen as guaranteed product characteristics. Amendments based on technical progress, modification of standards or production process or improvement of engineering are explicitly subject to change.