

# JDL26175

## MOLDED CASE CIRCUIT BREAKER 600V 175A



Download your JDL26175 datasheet



[Characteristics](#) | [Documents & Downloads](#)

### Main

Hide

<b>Product or component type</b>	Molded Case Circuit Breaker
<b>Range of product</b>	PowerPact J
<b>[In] rated current</b>	175 A
<b>Poles description</b>	2P
<b>Breaking capacity</b>	25 kA 240 V AC 18 kA 480 V AC 14 kA 600 V AC 20 kA 250 V DC
<b>[Ue] rated operational voltage</b>	250 V DC 600 V AC
<b>[Ics] rated service short-circuit breaking capacity</b>	80 %
<b>Trip unit technology</b>	Thermal-magnetic
<b>Product certifications</b>	CSA IEC UL listed
<b>Mounting mode</b>	Unit mount
<b>Electrical connection</b>	Lugs load Lugs line
<b>AWG gauge</b>	AWG 4...AWG 4/0 (aluminium/copper)
<b>Magnetic tripping current</b>	875...1750 A

### Offer Sustainability

Hide

<b>Sustainable offer status</b>	Not Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 0832 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product end of life instructions</b>	Need no specific recycling operations

### Contractual warranty

Hide

<b>Period</b>	18 months
---------------	-----------