



---

**PRODUCT-DETAILS****EXLB0710****40MM GS-PVC COAT EX COND 10M - BL**

---

**General Information**

<b>Extended Product Type:</b>	EXLB0710
<b>Product ID:</b>	7TCA297120R0078
<b>EAN:</b>	5011949001688
<b>Catalog Description:</b>	40MM GS-PVC COAT EX COND 10M - BL
<b>Long Description:</b>	Liquid Tight Metallic Conduit, Oil and Dilute Acid Resistant, Conduit Size 40mm, Minimum Bore 35.3mm, Reel Length 10 Meters, Galvanised Steel Core with Flame Retardant PVC Covering, Black
<b>Display Name:</b>	EXLB0710

---

**Additional Information**

<b>Product Main Type:</b>	KOPEX-EX FLEXIBLE CABLE PROTECTION
<b>Application:</b>	Connection for Conduit Systems when Oil and Acid Resistance is Needed

---

**Ordering**

<b>EAN:</b>	5011949001688
-------------	---------------

UPC: 786210287461

---

---

## Technical

---

Number of Batteries:	0
Color:	Black
Material:	Galvanized Steel Core with Flame Retardant PVC Covering

---

---

## Environmental

---

WEEE Category:	Product Not in WEEE Scope
RoHS Information:	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

---

## Container Information

---

Package Level 1 Units:	1 piece
Package Level 1 EAN:	5011949001688
Package Level 1 Height:	10.62 in 270 mm
Package Level 1 Depth / Length:	26.77 in 680 mm
Package Level 1 Width:	26.77 in 680 mm

---

---

## Certificates and Declarations

---

Declaration of Conformity - CE:	9AKK107492A9617
RoHS Declaration:	9AKK107992A8994
REACH Declaration:	9AKK107992A8994

---

---

## External Classifications and Standards

---

ETIM 8:	EC001179 - Protective metallic hose
ETIM 9:	EC001179 - Protective metallic hose
UNSPSC:	39131706

---

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems

