

Previously known as: MICROGARD® 2000 Overboots - Model 407

Protective overboots designed with superior breathable microporous laminate technology.

- **Improved defenses:** The AlphaTec® 2000 STANDARD Overboots Bound - Model 407 affords a proven protective barrier to low-concentration liquid chemicals, liquid and particulate biological hazards
- **Augmented protection:** These safety foot coverings are produced with comfortable moisture vapor permeable fabric, ensuring optimal breathability for better heat stress protection
- **Enhanced ergonomics:** For enhanced wearer comfort and safety, AlphaTec® 2000 STANDARD Overboots Bound - Model 407 is designed to ensure an optimized fit
- **Reduced contamination risks:** As they are low-linting, these protective overboots are particularly suitable for use in critical areas to reduce the risk of contamination



Industries

- Life Sciences
- Metal fabrication
- Food Processing

Applications

- Clean room cleaning and preparing
- Production line support & maintenance
- Maintenance of plant and machines
- Veterinary Services
- Cleaning of plant and machines
- Body painting including surface inspection

KEY FEATURES & BENEFITS

- **Protective barrier:** Guards against hazardous chemicals and biohazards
- **Comfortable, moisture vapor permeable fabric:** Reduced heat stress risk
- **Optimized fit:** For greater personal protection and comfort

Material Diagram



Seam Diagram



Performance Standards



EN ISO 13688:2013

Product Information

Product Information	
Available Sizes	One Size(42-46)
Color	White
Country Of Origin	China
Packaging Overview	150 pairs per case
Product Material	Microporous polyethylene Laminate non-woven
Product Reference	2000 Overboots - Model 407
Standards Overview	CE CATEGORY III (Type PB (6)-B, EN 14126)
Seam Type	Bound
Shelf Life	5 years
Style Number	W20B407

Suit components & accessories

Suit Components and Accessories	
Design Features	Tie fastening, elastic to top of boot, ESD PVC soles & bound seam

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region
Ansell Healthcare Europe NV
T: +32 (0) 2 528 74 00

North America Region
Ansell Healthcare Products LLC
T: +1 800 800 0444

Australia
Ansell Limited
T: +61 1800 337 041

Asia Pacific Region
Ansell Global Trading Center
T: +603 8310 6688

Latin America & Caribbean Region
Ansell Commercial Mexico S.A. de C.V.
T: +52 442 248 1544 / 248 3133

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

