

# 24-9020

Class 00 14" / 36cm Red



Category	A/C
Class	00
Cuff	Straight with beaded edge
Max Use	500V
Type	1
Colour	Red
Length	14" / 36cm
Sizes	8-11
Packaging	1 pair p/polybag and individual box. 10 pairs p/carton

### Features & Benefits

- Made from 100% natural high grade rubber latex
- Smooth chlorinated surface finish and rolled cuff edge aid donning and doffing
- Environmentally friendly dipping process free from the use of solvents
- Ergonomic design and finger shape minimises hand fatigue
- Increased flexibility in cold environments
- Silicone-free
- Double certification EN 60903 and ASTM D120



### Applications / Industries

- Power Utilities and Public Works
- Electric Public Transport Maintenance
- EV Battery Manufacturing and assembly
- EV Aftermarket Service and Maintenance
- Electrical Maintenance
- Excavation and Cable Laying
- Cable Jointing
- Field Services



### Performance



Manufactured and tested in accordance with IEC 60903, EN 60903 and ASTM D120.



### Special Categories Classes

Meets the special properties:

A-Acid C-Extreme low temperature  
H-Oil resistant Z-Ozone  
R = A + Z + H

CLASS	LENGTH CM/INCH		CATEGORIES	PROOF TEST VOLTAGE AC/DC	MAXIMUM USE VOLTAGE AC/DC	SIZES
Class 00 Beige	28/11	36/14	A/C	2.500/10.000	500/750	8, 9, 10, 11
Class 0 Red	28/11	36/14	A/C	5.000/20.000	1.000/1.500	8, 9, 10, 11
Class 1 White	36/14		A/C	10.000/40.000	7.500/11.250	8, 9, 10, 11
Class 2 Yellow	36/14		A/C/H	20.000/50.000	17.000/25.500	8, 9, 10, 11
Class 3 Green	36/14		A/C/H	30.000/60.000	26.500/39.750	8, 9, 10, 11
Class 4 Orange	41/16		A/C/H	40.000/70.000	36.000/54.000	9, 10, 11, 12

### Product Packaging

Each pair is supplied in an air sealed polybag and individual box.

Outer cartons contain 10 pairs of individual pair boxes.

