

Features

- Use as an extension and extended A-frame ladder
- Large box section stiles for strength and rigidity
- Strong anti-splay nylon restraint straps
- Robust cast aluminium stile guides for additional durability
- Extra-wide horizontal stabiliser bar and oversized feet for optimum stability
- 150kg Workload Capacity
- EN131 Professional

RS PRO Extension Ladders

RS Stock No.: 0217799



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

For professional & trade use. Ideal if you are looking for a quality ladder to use around the home or business. This professional-grade extension ladder is manufactured to current EN131 Professional standards and has a weight rating of 150kg. Our ladder includes a free stabilising bar that requires fitting before first use. These lightweight 2 and 3-section ladders are easy to carry around. They are made from super strong aluminium, giving you a stable platform that feels safer to work from. The 3-section ladders benefit from being able to convert into a freestanding ladder. This is ideal for when there is nothing to lean your ladder against, for example, painting fragile soffits and guttering. The rung guides are manufactured from steel for maximum strength and coated with Nylon for easier, faster action when extending or storing your ladder. The ladder has thicker box section stiles than cheaper alternatives, which makes the ladder stiffer, less likely to twist and longer-lasting

General Specifications

Rungs x Sections	7 x 3
Last Climbing Height (m)	3.92
Approx. Working Height (Ext. Ladder) (m)	5.67
Closed Length (m)	2.33
Extended Length (m)	5.02
Width (m)	0.45
Stabiliser Bar Width (m)	1.07
Weight (kg)	16.0