

Contact position indicator	Yes
Control type	Toggle
Local signalling	Trip indicator
Mounting mode	Removable comb busbar installed
Mounting support	DIN rail
9 mm pitches	8
Width	72 mm
Colour	White
Connections - terminals	Tunnel terminal with flap top or bottom 1...35 mm ² solid 1 Tunnel terminal with flap top or bottom 4 mm ² flexible without cable end 1...5 Tunnel terminal with flap top or bottom 4 mm ² solid 1...5 Tunnel terminal with flap top or bottom 6 mm ² flexible without cable end 1...3 Tunnel terminal with flap top or bottom 6 mm ² solid 1...3 Tunnel terminal with flap top or bottom 0.5...25 mm ² flexible with cable end 1 Tunnel terminal with flap top or bottom 0.5...25 mm ² flexible without cable end 1
Wire stripping length	14 mm top or bottom
Tightening torque	3.5 nm top or bottom
Earth-leakage protection	Separate block

Environment

Standards	EN 60898-1 EN 60947-2 IEC 60898-1 IEC 60947-2
IP degree of protection	IP3 EN 60947-2 IP3 IEC 60947-2
Pollution degree	3 EN 60947-2 3 IEC 60947-2
Electrical shock protection class	Class II front face
Tropicalisation	2 EN/IEC 60068-2-78
Relative humidity	95 %
Operating altitude	0...2000 m
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-40...85 °C
RoHS EUR status	Compliant
RoHS EUR conformity date	1001