



CHARACTERISTIC

Maximum angular free movement	$\pm 30^\circ$
Maximum contact resistance	2m Ω
Typical connecting force	800g
Typical disconnecting force	100g
Current rating	7A
Spills to fit and work in boards	0.062" Thick
	and holes 1.25 - 1.4mm dia.
Sockets to accept wires up to	16/0.2 0.5mm ² O.D. 1.5mm

MATERIALS

Socket	Silver plated brass
Insulation	PTFE
Spill	Palladium plated brass