## Multifunctional Wiping Cloth



## **Features**

- Excellent overall performance across different industries and applications
- Ideal for cleaning as you go, catching spills and drips as well as cleaning work surfaces, sinks, utensils and machinery
- Exceptional food and dirt pick-up



## **Specifications**

			1	•
Typical Properties		Unit	Value	Test Methods &Voluntary standards
Basis Weight		g/ m <sup>2</sup>	67±3	FZ/T60003-91 GB/T 26379
Colour		_	Blue 2#	
Bases	Wood Pulp	%	55±2%	Corporation Standards
	PET	%	45±2%	
Thickness		mm	0.28±5%	FZ/T60004-91 GB/T 24218.2-2009
Fracture Strength	MD	N/5cm	≥150	FZ/T60005-91 GB/T26379
	CD	N/5cm	≥70	
Fracture Elongation	MD	%	≤50	FZ/T60005-91 GB/T 24218.3-2010
	CD	%	≤100	
Speed of Absorbability		mm/30s	≥45	- GB/T 24218.6-2010
Absorptive Capacity		%	≥450	
Fluorescent Substance		_	NO	
Surface Active Substances		%	-	YY0331-2002P
Residue on Ignition		%	-	
Testing Temperature: 23°C	Testing Hum	idity: 55%	1	

Art Nr. Size		Form
RND 605-00182	300 x 350 mm	300 pcs/Box