

213040000

Polyester Enclosure Polyglas / Polycase 300 x 400 x 200 mm

Polyester Enclosure Polyglas / Polycase 300 x 400 x 200 mm

Catalogues | Declaration of Conformity | Drawing | 3D Data

Technical data

Height	300 mm
Width	400 mm
Depth	200 mm
Material	Polyester
Colour	Agate grey (RAL 7038)
Ingress protection	IP66
Degree of protection norm	EN 60529
temperature min.	-30 °C
temperature max.	90 °C
Seal material	CR-(Chloroprene)
Insulation	Fully insulated according to VDE 0100
Toxicity	Halogen free
Surface resistance	>10^12 Ohm
Surface resistance norm	IEC 60093
Special colours on request	Yes
Approvals	UL (508A)

Commercial data

Order unit	1 Piece
Customs tarif number	39269097
Weight	4.5 kg
GTIN	4250157915474

ETIM classification

ETIM 8	EC000261

ROSE SYSTEMTECHNIK GMBH
Erbeweg 13-15
32457 Porta Westfalica, Germany


Tel.: +49 571 50 41-0
Fax: +49 571 50 41-6
Mail: rose@rose-pw.de

Accessories

100112030
Mounting plate for 21.304000

Zubehör - s. Zeichnung
Accessories - see drawing

216100010
Standard handle for Polyglas



216100020
Standard handle with lock for Polyglas

Zubehör - s. Zeichnung
Accessories - see drawing

216100030
Triangular lock for Polyglas (8mm)

Zubehör - s. Zeichnung
Accessories - see drawing

216100040
Square lock for Polyglas (8mm)

Zubehör - s. Zeichnung
Accessories - see drawing

216100060
Daimler Benz lock for Polyglas

Zubehör - s. Zeichnung
Accessories - see drawing

216100070
Double ward lock for Polyglas (3mm)

Zubehör - s. Zeichnung
Accessories - see drawing

216100140
Square lock for Polyglas (7mm)