

product type designation



Split Connect Tap

PROFIBUS PA SplitConnect TAP; for setting up PROFIBUS PA segments and connection of PA field devices, insulation displacement method, IP67 Type of delivery: 10 units=1 pack .

transfer rate	
transfer rate	
<ul style="list-style-type: none"> with PROFIBUS PA 	31.25 kbit/s
interfaces	
number of electrical connections	
<ul style="list-style-type: none"> for PROFIBUS cables 	3
type of electrical connection	
<ul style="list-style-type: none"> for PROFIBUS cables 	integrated insulation displacement contacts
mechanical data	
material / of the enclosure	PBT (polybutyleneterephthalate)
design, dimensions and weights	
width	84 mm
height	54 mm
depth	49 mm
net weight	250 g
fastening method	
<ul style="list-style-type: none"> 35 mm top hat DIN rail mounting wall mounting 	Yes Yes
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> during operation during storage during transport 	-40 ... +85 °C -40 ... +85 °C -40 ... +85 °C
protection class IP	IP67
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> silicon-free 	Yes
standards, specifications, approvals	
certificate of suitability	
<ul style="list-style-type: none"> UL approval 	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Image database to website: CAx-Download-Manager to website: Industry Online Support 	http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

11/9/2023 