

M12 BLROT-O

M12™ BRUSHLESS ROTARY TOOL

- Compact and balanced in all orientation design allow the user to hold the tool close to the work piece
- Variable speed from 5000 rpm to 27,500 rpm with 12 speed settings allows the user to dial in the correct speed for each application
- 3.2 mm collet included, compatible with most common accessories
- Soft grip and low vibration allows user to work comfortably and for longer periods
- LED light illuminates the work piece
- Low weight only 0.36 kg
- Spindle lock for easy accessory change



REDLITHIUM™



Collet capacity (mm)	3.2
No load speed (m/min)	5000 - 27500
Speed settings	12
Weight with battery pack (EPTA) (kg)	0.562 (M12 B2)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article Number	4933493591