

Hose tail coupler



Technical characteristics

Technology: "One push" safety system (avoids hose whip)

Operating pressure: 2 to 16 bar


Flow rate at 6 bar: 3686 l/min ($\Delta P = 0,6$ bar)

ID Passage: 11 mm

Temperature: -15°C to +70°C

Construction: Body : Stainless steel

Highlight: Anti-static, Excellent efficiency, Harsh conditions

	A (mm)	B (mm)	C (mm)	For hose ID (mm)	Parts Numbers
	136	37	10	10	ISI 111810
	120	37	12,5	13	ISI 111813
	120	37	15,5	16	ISI 111816
	161	37	18,5	19	ISI 111819