



Main

Range of product	Canalis
Product name	KS
Product or component type	Electrical and mechanical jointing
Product compatibility	KS
[Ie] rated operational current	400 A
Offer type	Spare part
Colour	White (RAL 9001)

Complementary

Device application	Medium power distribution
[Ue] rated operational voltage	230...690 V
Control type	Without
Number of circuits	1
Busbar trunking polarity	3L + N + PE
Width	178 mm
Depth	60 mm
Height	165 mm
Net weight	2 kg

Environment

IK degree of protection	IK08 conforming to IEC 62262
IP degree of protection	IP55 conforming to IEC 60529
Standards	IEC 61439-6 IEC 60439-2

Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Halogen content performance	Halogen free product

Contractual warranty

Warranty	18 months
----------	-----------

