



Product Highlights:

- High-speed, Class 10, UHS Speed Class 3 (U3) and Video Speed Class 30 (V30) performance—leverages UHS-I technology for a read transfer speed up to 100MB/s (667x)¹
- Capture high quality images of stunning 1080p full-HD, 3D, and 4K video
- Enjoy shooting longer without changing cards—large capacity options up to 256GB
- High-speed file transfer from card to computer to dramatically accelerate workflow
- 10-year limited warranty (For regions OUTSIDE of the Americas)
- Limited-lifetime warranty (For Americas ONLY)

Capacities:

SDXC
64GB
128GB
256GB



High-speed performance you can trust

Designed for your mid-range DSLR, HD camcorder, 3D camera, Lexar® Professional 667x SDXC™ UHS-I cards let you quickly capture, and transfer high-quality photos of stunning 1080p full-HD, 3D, and 4K video, with read speeds of up to 667x (100MB/s)¹. With Class 10, UHS Speed Class 3 (U3) and Video Speed Class 30 (V30) rating, these cards leverage UHS-I technology to deliver high-speed performance. This dramatically accelerates workflow from start to finish, so you can save time and get back to the business of photography.

Shoot high-quality images and 1080p full-HD, 3D, and 4K video. Make the most of your adventures in the great outdoors by leveraging the power and performance of these cards. Whether you're using a mid-range DSLR, HD camcorder, or 3D camera, you'll be able to leverage the latest photo and video features available for shooting high-quality images and stunning 1080p full-HD, 3D, and 4K video².

Capture extended lengths of video with high-capacity options. With growing video capabilities, you need high-performance cards you can rely on, and high-capacity options to keep you shooting longer without changing cards.

Save time dramatically accelerated workflow. The high-speed performance of Lexar Professional 667x SDXC UHS-I cards dramatically accelerate your workflow from start to finish, so you can save time and get back to the business of photography.

Get more from your device. With its speed rated at Class 10, UHS Speed Class 3 (U3) and Video Speed Class 30 (V30), these cards leverage UHS-I technology to deliver a transfer speed up to 100MB/s (667x)¹, these high-capacity cards give you the speed and space you need to capture, transfer, and share more adventures on the go.

Rigorously tested. All Lexar product designs undergo extensive testing in the Lexar Quality Labs, facilities with more than 1,100 digital devices, to ensure performance, quality, compatibility, and reliability.

For more than 20 years, Lexar has been trusted as a leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, and solid-state drives. With so many options, it's easy to find the right Lexar solution to fit your needs. Lexar products are available worldwide at major retail and e-tail stores. For more information or support, visit www.lexar.com.

¹ Up to 100MB/s read transfer, write speeds lower. Speeds based on internal testing. Actual performance may vary. X=150KB/s. Actual usable memory capacity may vary. 1GB equals 1 billion bytes.

Warranty:

(For Americas ONLY) Limited-lifetime warranty
(For regions OUTSIDE of the Americas) Warranty is limited to 10 years from purchase in regions excluding the Americas

www.lexar.com

©2019 All Rights Reserved. Information, products, specifications, and features are subject to change without notice. Neither Lexar nor Longsys is responsible for omissions or errors in typography or photography. Lexar, the Lexar logo, and all other Lexar trademarks are the property of Longsys Electronics (HK) Co., Ltd. or Shenzhen Longsys Electronics Co., Ltd. All other trademarks are property of their respective owners.