

Dissipative Stretch Film

Part No. 3170.xxxx



- Electrostatic dissipative film
- Complies with EN 61340-5-1
- Good mechanical properties
- Suitable for machine and hand wrapping
- Recyclable
- Colour: Pink

**Electrical properties:**

	Test standard	Typical values	Requirements
Surface resistance R_s	EN 61340-5-1 EN 61340-2-3	$10^{10} - 10^{11} \Omega$	$10^5 \leq R_s \leq 10^{11} \Omega$ EN 61340-5-1
Decay time	EN 61340-2-1	< 2 sec.	< 2 sec.

Technical data:

Property	Test Method	Typical values
Mechanical		
Thickness	ASTM D-882	25 μm
Tensile Strength	ASTM D-882	
MD		35 N/mm^2
TD		30 N/mm^2
Elongation	ASTM D-882	
MD		600 %
TD		700 %
Tackiness	In house test	16 gr/5 cm
Puncture Energy	In house test	400 N/mm

MD = Machine Direction

TD = Transversal Direction