

S-Video / Composite to USB Video Capture Cable w/ TWAIN and Mac Support

Product ID: SVID2USB23



The SVID2USB23 USB 2.0 S-Video & Composite Video Capture Cable offers an easy to use analog video capture solution, enabling you to grab video from an S-Video or Composite video source, as well as the accompanying 2-channel RCA audio, to your Mac® or Windows® computer.

The cable connects to your desktop or laptop computer through USB 2.0, and is compact enough to fit in the palm of your hand, providing a conveniently portable video capture solution that's more than suitable for use with laptops and desktop computers alike.

An easy-to-use device for recording analog video to your computer from external sources, such as a VCR or camcorder the SVID2USB23 offers the perfect solution for Betamax or VHS video capture, with real-time MPEG-1, MPEG-2, and MPEG-4 encoding, as well as TWAIN support, to ensure compatibility with a wide range of systems and software.

This analog video capture cable supports a broad range of operating systems, delivering seamless analog video capture for Mac® computers (OS 10.X), and Windows® PCs (Windows® 7/8/8.1/10, Windows® 2000/XP(32/64-bit)/Vista(32/64-bit)).

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Convert VHS home movies to digital format - Connect your VCR, camcorder, or any other analog video source to your Mac or PC and capture your audio/video in MPEG 1/2/4 format
- Import recorded videos onto your Mac® or Windows® computer for editing, and make your own compilation

Features

- Works with Mac® or Windows® computers
- Choose from MPEG-1, MPEG-2, or MPEG-4 video encoding
- Features TWAIN support for use with various software titles
- Supports NTSC, PAL, and SECAM video capture
- Up to 30 fps analog video capture capability at maximum resolution of 720x480(NTSC) / 720x576(PAL)
- Plug and Play device installation, requires no power adapter
- Snapshot function allows you to capture still images from video
- Small and lightweight design offers convenient portability for on-the-go applications

Hardware	Warranty	2 Years
	Audio	Yes
	AV Input	Audio RCA Composite S-Video
	AV Output	USB
	Chipset ID	eMPIA - EM2861
	Industry Standards	NTSC, PAL, SECAM
		Video Encoding: MPEG 1, MPEG 2, and MPEG 4 DirectShow Compatible
Performance	Maximum Analog Resolutions	720x480(NTSC) / 720x576(PAL)
	Maximum Data Transfer Rate	480Mbps
Connector(s)	Connector A	1 - USB Type-A (4 pin) USB 2.0 Male Output
	Connector B	1 - Composite Video (1 x RCA) Female Input 1 - Stereo Audio (2 x RCA) Female Input 1 - S-Video (4 pin, Mini-DIN) Female Input
Software	OS Compatibility	Windows® 2000, XP, Vista, 7, 8, 8.1, 10 Apple® OSX 10.6 - 10.14
Special Notes / Requirements	Note	The MPEG 4 video file format is supported on the included SVID2USB23 Capture software for Mac and other third party DirectShow™ capture software such as OBS movavi® video software does not support the MPEG4 video file format
Environmental	Humidity	5~85% RH Non-condensing
	Operating Temperature	0°C to 50°C (32°F to 122°F)
	Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Physical Characteristics	Cable Length	527 mm [20.7 in]
	Color	Black
	Enclosure Type	Plastic
	Product Height	1.4 cm [0.6 in]
	Product Length	80 mm [3.1 in]
	Product Width	34 mm [1.3 in]
	Weight of Product	66 g [2.3 oz]

Packaging Information	Package Height	41 mm [1.6 in]
	Package Length	14.6 cm [5.7 in]
	Package Width	20.8 cm [8.2 in]
	Shipping (Package) Weight	177 g [6.2 oz]
What's in the Box	Included in Package	1 - USB Video Capture Cable
		1 - Software CD
		1 - Driver CD
		1 - Instruction Manual

Product appearance and specifications are subject to change without notice.