

MLFB-Ordering data

6SL3203-0BB21-8VA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

<b>Rated data</b>	<b>Connections</b>
-------------------	--------------------

<b>Input</b>	
Number of phases	1 AC
Line voltage	200 ... 240 V
<b>Output</b>	
Rated current	18.0 A

<b>Mechanical data</b>
------------------------

<b>Dimensions</b>	
Width	59.0 mm
Height	155.0 mm
Depth	53.0 mm
Degree of protection	IP20 / UL open type
Net weight	0.9 kg

<b>Line side</b>	
Version	screw-type terminal
Conductor cross-section	0,3 ... 10,0 mm <sup>2</sup>
<b>Load side</b>	
Version	Screw-type terminals
Cable length	20.00 m
<b>PE connection</b>	
Version	On housing with M5 screw studs